



## Product data sheet

# Triflex Cleaner (Reiniger)

### Use

Triflex Cleaner is used with Triflex products for substrate pre-treatment, degreasing metals and cleaning tools.

### Components

Component	Product
Cleaner	Triflex Reiniger

### Packaging

Component	Pack size
Cleaner	Canister: 9.00L
	Canister: 27.00L

### Colour

Transparent

### Application method

Wearing the appropriate personal protective equipment, pour onto a clean cloth and apply an even layer by wiping the surface to remove any contamination. Regularly replace the cloth. Large areas can be treated by mopping.

### Consumption

Depending on the degree of soiling and the type substrate, allow 0.20L/m<sup>2</sup> minimum.

**Note:** Consumption based on smooth even, non-absorbent substrate.

### Drying time at 20°C

Approximately 20 minutes.

Where used as a pre-treatment, overlay between 20 and 60 minutes after cleaning.

### Tool cleaning

Decant the cleaner into a suitable clean receptacle.  
Clean contaminated tools with Triflex Cleaner immediately after use.

### Storage / shelf life

Store unopened in a cool, dry, well ventilated place above freezing, out of direct sunlight and in the original container.

Shelf life if stored correctly: minimum 12 months.

### Health and safety

Refer to Safety Data Sheets.

### Disposal information

Refer to Safety Data Sheets for recommended EWC waste codes.



### Notes

The advice we provide on the application of our products is based on extensive development work and many years of experience, and is given to the best of our knowledge. The wide variety of requirements for a building under the most diverse conditions mean that it is necessary for the contractor to test the product for suitability in each case. Triflex reserve the right to make alterations in keeping with technical developments or improvements.

Non-Triflex products must not be used with Triflex systems.

Only the most recent version of this data sheet is valid.